



Strainer Systems

- One piece strainer
- Sealed against backflow
- Easily cleaned
- 30 to 1000 micron gauge
- Very large strainer surface in a compact design



AB6 strainer elements are designed around a triangular profile with a flat surface, it is spiraled into a cylindrical shape with internal axial support webs. The media goes through the gauged flat surface keeping solids inside the basket (standard flow). When triangular surface is exposed to cleaning stream, the stream is concentrated against the solids forcing their dislodgement. This strainer design provides for very precise gauging, long term durability, and excellent cleanability in a one piece unit.

Interex
Est. 1976
TRADING & MARKETING
www.interex-usa.com
info@interex-usa.com

Various versions adapted to meet your operating requirements

Type FCE

Right angle strainer

Standard flow: to the inside of the strainer towards the outside.
Optional flow: to the outside of the strainer towards the inside, by switching out the strainer unit.

- Input/ output at 90° angle • Easy to disassemble • Easy to clean



Type FCL.C

In-line

Standard flow: to the inside of the strainer towards the outside.
Optional flow: to the outside of the strainer towards the inside, by switching out the strainer unit.

- Requires unions/clamps to facilitate disassembly • Easy to clean



Type FCY

"Y" type strainer

Standard flow: to the inside of the strainer towards the outside.
Optional flow: to the outside of the strainer towards the inside, by switching out the strainer unit.

- Input/ output at 90° angle • Easy to disassemble • Easy to clean

Type FCL.E

In-line "offset"

Standard flow: to the inside of the strainer towards the outside.
Optional flow: to the outside of the strainer towards the inside, by switching out the strainer unit.

- Requires unions/clamps to facilitate disassembly • Easy to clean
- No "low point", or pooling



Special Filter/Strainer Units

Automatic switchover unit



Special configurations to meet customer requirements

